

PCUS[®] pro HF – High-frequency ultrasonic device

Compact high-frequency ultrasonic frontend for fast automated testing of special welds and thin materials.

Between classical ultrasonics and acoustic microscopy

The ultrasonic frontend device PCUS[®] pro HF closes the gap between classical ultrasonic testing and acoustic microscopy. The inline-capable, compact frontend allows the automated testing of thin sheet metal, composite materials, complex joints or electronic components.

Thanks to the extreme compact design and very low power consumption the device can be mounted directly near the probe. With the integrated 4-axis scanner interface and the fast USB 3.0 super speed connection for data transfer rates of up to 320 MB/s, this device can be integrated seamlessly into industrial testing stations.



PCUS[®] pro HF frontend – front side.

PCUS[®] pro HF Details

Category	Characteristics	Value
General	Dimensions (L, W, H)	190 x 150 x 43 mm ³
	Weight	940 g
	Operating temperature and humidity range	5...50 °C @ 75 % relative humidity (non-condensing)
Transmitter	Number of transmitters	1
	Transmitter pulse voltage into 50 Ω	-50 to -180 V adjustable
	Pulse	Negative rectangle pulse
	Output impedance	< 10 Ω
	Pulse width	0 to 50 ns, in steps of 1 ns
	Pulse fall time	< 1.5 ns
	Pulse delay	0 to 10 μs, in steps of 8 ns
	Pulse repetition frequency	Up to 20 kHz

PCUS® pro HF Details

Category	Characteristics	Value
Receiver	Number of receivers	1
	Input mode	Pulse/Echo or Transmit/Receive mode
	Frequency range	5 to 150 MHz
	Input impedance	50 Ω
	Filters	Four analog filters, software selectable, values on user's demand
	Preamplifier gain	0/20 dB switchable
	Main amplifier gain	0...50 dB, maximum input signal 2 Vpp (100 % screen height)
	TGC	-
Signal path	Probe delay	0 to 250 μ s, in steps of 8 ns
	Maximum recording length	65,520 samples
	A/D converter	12 bit, 500 MS/s
	Gates	One echo start gate and four measurement gates
	Rectification	None, positive-, negative-, or full-wave
Interface and connectors	Transducer connector	2x SMA female
	PC interface	USB 3.0 super speed/high-speed/full speed, USB 3.0 B-type connector
	Trigger in/out	TTL level on DSUB 44 I/O connector
	General purpose I/O (GPIO)	3 digital inputs, 3 digital outputs, 2 auxiliary analog inputs on DSUB 44 I/O connector
	Scanner interface inputs	4 axis, RS422 level on DSUB 44 I/O connector
	Power supply	24 V DC, max. 400 mA on locking DC plug 2.1mm, CLIFF FC681478
Software	Digitally signed drivers for Windows® (Windows® 7 or higher), x86 and x64	
	For proper USB 3.0 operation, Windows 8.0 or higher is strongly recommended!	
	Managed Windows® SDK based on .NET 4.8	
	PCUS® pro Lab testing software	

Disclaimer

Distribution and copying of this document, utilization and reporting of its contents are prohibited – even in parts – if not explicitly allowed. Violation commits to amends. All rights reserved, especially if a patent is assigned or a trademark is registered.

Christian Richter

Fraunhofer Institute for Ceramic Technologies and Systems IKTS
Maria-Reiche-Strasse 2, 01109 Dresden, Germany
Phone +49 351 88815-635
christian.richter@ikts.fraunhofer.de

341-D-24-08-15

